



Digital Conductivity Meter



Portable Conductivity Meter has been developed to facilitate easy determination of conductivity of non-ferrous metals based on eddy current principle. Instrument uses a probe which when placed on the surface of metal indicates conductivity on a linear scale panel meter.

The instrument can be used to measure stressed conditions if they can be related to the electrical conductivity of the specimen. Whilst the accuracy claimed is 2% however, for high conductivity samples as accuracy of better than 1% is easily obtained. The users can also, if desired, use their own sample of known conductivity in the region of interest to enhance the accuracy.

The instrument is supplied in a rugged carrying case which gives complete protection and has separate pocket for probe. The equipment can be used without removing it from the carrying case.

Digital Conductivity Meter

Special Features:

- Direct reading
- High Accuracy
- Very Compact
- Built in Power Supply of 9V Dry Battery.
- Fast Response
- Measurement time less than 5 seconds per sample.
- Probes of different diameters (8mm, 10mm & 12mm)

Applications:

Some of the typical applications are listed below:

- 1. Measurement of absolute conductivity of electrical hardware and electrical conductor made of copper, aluminum and their alloys.
- 2. Segregation of mixed lot of non-ferrous metals.
- 3. Determination of uniformity of heat treatment.
- 4. Determination of homogeneity of metal.
- 5. It can be used to ingots, forgings, sheets, castings, bars of finished parts, of any conductive material such as aluminum, copper, brass, gold, silver and magnesium. It can also be used to detect the subsurface cracks on the metal.

Operating Instructions:

- 1. Hold the probe in knurled portion firmly.
- 2. Press it gently on the metal under test, keeping it vertical to the plain of metal surface. Align the probe in this condition will show lowest conductivity and will also be most accurate.
- 3. It is recommended that prior to taking measurements, the equipment should be calibrated at 99% and 30% conductivity with help of two controls and the two standard samples provided on in the instrument.
- 4. Instrument works on 9V dry battery pack. Periodically battery may be checked with a push button provided on the front panel. If low battery indication observe from the instrument, it needs to be replaced.

Specifications:

Weight of the instrument	1.5kg
Diameter of Test probe	8mm, 10mm, and 12mm. (one of the probes will be available with the instrument)
Thickness of Sample	2mm for 20% and 0.8mm for 100% conductivity.
Range of Conductivity	20% to 105%
Accuracy	Indicated Value: 1.5%
Power	9V Dry Battery
Display	3½ digit



To keep pace with the latest technology Sivananda Electronics reserves the right to update it's system. Hence, information in the brochure is likely to change without notice.

SIVANANDA ELECTRONICS

DEEPAK MAHAL, LAM ROAD, DEVLALI-422 401. NASHIK, MAHARASHTRA, INDIA.

Phone: 0253-2491423, 2491504, 2491816, Fax: 0253-2492291. E-mail: mkb@sivanandaelectronics.com. Web: www.sivanandaelectro.com MUMBAI

: 208, SAHAR PLAZA COMPLEX, ANDHERI KURLA ROAD, ANDHERI, MUMBAI-400 059. PHONE: 022-28271046, 66430590 / 91. FAX: 022-28389232 E-mail: sivabom@vsnl.com

NEW DELHI : G-145, KALKAJI, NEW DELHI-110 019, PH/NE: 011-26221582, 26434442. E-mail: sivadelhi@bol.net.in BANGALORE : 44/2, DICKENSON ROAD, BANGALORE-650 042. PHONE: 080-25585673, 25597416. E-mail: sivadelni@vsnl.net HYDERABAD : 102, ART PLAZA, YWCA LANE, NEAR HIRA HALL, BOGGUL KUNDA, ABIDS, HYDERABAD-500 001. PHONE: 040-30629539

MFRS. OF : ELECTRONIC INSTRUMENTS, METAL DETECTORS, TURNSTILES, PERIMETER PROTECTION SYSTEMS